



Summary

[Request a quote](#)

[Catalog](#)

Size	3T
Series	T - Small Outdoor keyed

Technical details

Form & Material

Shell style / Model id	BFG - Blanking cap for plugs
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Weight	2.1 g

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/bfg-3t-100-cas.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Environmental protection (IP rating)	IP68
Minimal temperature	-50°C / +135°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Resistance to vibration	15 g [10 Hz - 2000 Hz]
Shock Resistance	100 g [6 ms]
Salt Spray Corrosion	>1000 hr

Drawings



Dimensions

	A	B	L	N
mm.	17	6	17.6	120
in.	0.67	0.24	0.69	4.72