



Summary

[Request a quote](#)

[Catalog](#)

Size	1K
Series	K - Outdoor keyed

Technical details

Form & Material

Shell style / Model id	BFL - Cap for plug (L key)
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Keying	2 keys (gamma=75, plug: female contacts, receptacle: male contacts)
Weight	10.99 g

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/bfl-1k-100-nas.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental protection (IP rating)	IP68
Minimal temperature	-55°C / +135°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>144 hr

Drawings



Dimensions

	A	B	L	N
mm.	16	6	15.5	85
in.	0.63	0.24	0.61	3.35

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/bfl-1k-100-nas.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.