



Summary

[Request a quote](#)

[Catalog](#)

Low Voltage	36
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Size	1R

Technical details

Electrical Configuration

Contact Termination Low voltage	PCB - Straight
Insert configuration value	1R.336 - 36 low voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	2.5 Amps
Contact Type	Print (straight)
Contact Dia.	0.7
Low Voltage	36

https://www.lemo.com/int_en/ebg-1r-336-gln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Form & Material

Shell style / Model id	EBG - Fixed receptacle, key (G) or key (A) with visible shell
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Crastin® PBT (Polybutylene terephthalate), gray
Locking system	Push-pull
Keying	3 keys (alpha=50,beta=30, plug: male contacts, receptacle: female contacts)
Weight	14.05 g

Environment

Environmental protection (IP rating)	IP50
--------------------------------------	------

Drawings



Dimensions

	A	B	C	E	G	L	M
mm.	37	15	51	4.5	3.2	19.5	14.5
in.	1.46	0.59	2.01	0.18	0.13	0.77	0.57

https://www.lemo.com/int_en/ebg-1r-336-gln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.