



Summary

[Request a quote](#)

[Catalog](#)

Triax	1
Plug	Plug - Fixed
Locking system	Push-pull
Size	T7

Technical details

Electrical Configuration

Triax	1
Contact Termination Triax	Solder
Contact Type	Solder

Form & Material

Shell style / Model id	FCZ - Fixed plug, crimp, nut fixing
Plug	Fixed
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	104.22 g

https://www.lemo.com/int_en/fcz-t7-675-cta01s.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Environmental protection (IP rating)	IP68
Minimal temperature	-55°C / +250°C
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 20000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet

Drawings



Dimensions

	A	E	L	M	e
mm.	35	18.5	38	6	M28x1.0
in.	1.38	0.73	1.5	0.24	