



Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|-----------------|
| Coax | 1 |
| Plug | Plug - Straight |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 2.20 - 2.60 mm |
| Size | 0A |

Technical details

Electrical Configuration

| | |
|----------------------------|--------------------------|
| Coax | 1 |
| Contact Termination Coax | Solder |
| Insert configuration value | 0A.250 - 1 Coax (50 Ohm) |
| Contact Type | Coaxial 50 Ohm (Solder) |
| Bucket Dia. | 1.1 |

https://www.lemo.com/int_en/ffa-0a-250-ctac27z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | FFA - Straight plug with cable collet and nut for fitting a bend relief |
| Plug | Straight |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | 3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts) |
| Variant | Nut for fitting a bend relief |
| Weight | 9.26 g |

Environment

| | |
|--------------------------------------|----------|
| Environmental protection (IP rating) | IP50 |
| Salt Spray Corrosion | >1000 hr |

Cable fixation

| | |
|------------------------------------|-----------------------|
| Cable termination protection | For cable bend relief |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 2.20 - 2.60 mm |

Recommended By Lemo

Accessories

Tools

https://www.lemo.com/int_en/ffa-0a-250-ctac27z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

| Cable PartNumber | Material | Colour | Cable image |
|-------------------------|-----------------|---------------|--------------------|
| 18800 | PTFE | White | |
| CCX.50.RG0.58AU14B | FEP | white | |
| CCX.50.RG1.74-U25N | PVC | Black | |
| CCX.50.RG1.74U25N | PVC | Black | |
| CCX.50.RG1.88AU24B | TFE | white | |
| CCX.50.RG1.88AU26B | PFA | White | |
| CCX.50.RG1.88AU26B | PTFE | White | |
| CCX.50.RG3.16BU26M | FEP | Brown | |
| CCX.75.RG1.79BU26M | FEP | Brown | |
| CCX.75.RG1.87AU26B | PFA | White | |

https://www.lemo.com/int_en/ffa-0a-250-ctac27z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.