



Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|--------------------------------|
| Coax | 1 |
| Plug | Plug - Straight |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 2.80 - 3.10 mm |
| Matching parts | ERA.00.250.CTL |
| Series | 00 - NIM-CAMAC |

Technical details

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/ffc-00-250-ctac29.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Electrical Configuration

| | |
|----------------------------|------------------------------|
| Coax | 1 |
| Contact Termination Coax | Solder |
| R (max) | 6.1 mOhm |
| Insert configuration value | 0.25 - 1 Coax (50 Ohm) |
| Insulator | T: PTFE |
| Rated current | 4 Amps |
| Impedance | 50 Ohm |
| VSWR | $1.09 + 0.11 * f/\text{GHz}$ |
| Vtest | 2100 V (AC), 3000 V (DC) |
| Contact Type | Coaxial 50 Ohm (Solder) |
| Test voltage | 2.1 kV (rms) |
| Cable type | Cable type: A RG 316 /U S |
| Bucket Dia. | 0.6 mm (0.024in) |
| Contact Dia. | 0.7 mm (0.028in) |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | FFC - Straight plug with flats on latch sleeve and cable collet |
| Plug | Straight |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | Circular, male |
| Weight | 2.89 g |

Environment

| | |
|--------------------------------------|----------|
| Environmental protection (IP rating) | IP50 |
| F ret (min) | 100 N |
| Salt Spray Corrosion | >1000 hr |

Cable fixation

| | |
|------------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 2.80 - 3.10 mm |

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/ffc-00-250-ctac29.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo



Accessories

Tools

Spanner wrench

[DCD.00.ZZZ.PA050](#)

Cables

| Cable PartNumber | Material | Colour | Cable image |
|--------------------|----------|--------|---|
| 17420 | PVC | Black |  |
| 31600 | PTFE | Brown | |
| CCX.50.RG1.74AU28N | PVC | Black | |
| CCX.50.RG1.74AU28N | PVC | Black |  |
| CCX.50.RG3.16U28M | PTFE | Brown | |

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/ffc-00-250-ctac29.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.