



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	16
Wire Size/AWG	24 - 24
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	7.60 - 8.00 mm
Size	2T
Suggested matching part	<a href="#">EGG.2T.316.CLL</a>
Series	T - Small Outdoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/fgg-2t-316-clac80z.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-2t-316-clac80z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	16
Contact Termination Low voltage	Solder
R (max)	6.1 mOhm
Insert configuration value	2T.316 - 16 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	6 A
Vtest (contact-contact)	1.4 kV (DC)
Vtest (contact-shell)	1.8 kV (DC)
Max. Conductor	0.34 mm <sup>2</sup> (AWG 22)
Max. Stranded Conductor	0.34 mm <sup>2</sup> (AWG 22)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	24 - 24
Gender	Standard

## Form & Material

Shell style / Model id	FG - Straight plug, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	30.56 g

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/fgg-2t-316-clac80z.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-2t-316-clac80z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	>3000 mating cycles
Temperature range	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Resistance to vibration	15 g [10 Hz - 2000 Hz]
Shock Resistance	100 g [ 6 ms]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.60 - 8.00 mm

## Drawings



## Dimensions

	A	L	M	S1	S2
mm.	15	54	42	14	12
in.	0.59	2.13	1.65	0.55	0.47

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/fgg-2t-316-clac80z.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-2t-316-clac80z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

Accessories	
Compatible cap	<a href="#">BFG.2T.100.CAS</a>
Tools	
Spanner	<a href="#">DCP.2T.110.TN</a>

## Cables

Cable PartNumber	Material	Colour	Cable image
CMN.16.T22.076QGZE	TPR (medical)	Grey	