



Summary

[Request a quote](#)[Catalog](#)

Coax	1
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Jacket cable outside diameter [mm]	10.60 - 12.00 mm
Size	3E
Matching parts	FFA.3E.275.CLAK11E
Series	E - Outdoor Stepped Insert

Technical details

Electrical Configuration

Coax	1
Contact Termination Coax	Solder
Insert configuration value	3E.275 - 1 Coax (75 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	15 Amps
Impedance	75 Ohm
VSWR	1.04 + 0.05 * f/GHz
Vtest	2700 V (AC), 3900 V (DC)
Contact Type	Solder
Cable type	Cable type: A RG 213/U, RG 115 A/U, RG 11 A/U, RG 144/U, RG 165 /U S

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/pca-3e-275-cllk11e.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	PCA - Free receptacle with oversize cable collet
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, female
Variant	Gasket and O-ring in EPDM
Weight	132.23 g



Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental protection (IP rating)	IP68
Minimal temperature	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	10.60 - 12.00 mm

Drawings



https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/pca-3e-275-cllk11e.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Dimensions

	A	B	L	S1	S2
mm.	23	22	84	19	19
in.	0.91	0.87	3.31	0.75	0.75