



Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	30
Gender	Reverse Gender
Locking system	Push-pull
Size	3B
Series	B - Indoor keyed

Technical details

Electrical Configuration

Insert configuration value	3B.330 - 30 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	3.5 Amps
Vtest (contact-contact)	800 V (AC), 1130 V (DC)
Vtest (contact-shell)	700 V (AC), 990 V (DC)
Contact Type	Solder
Contact Dia.	0.7 mm (0.03in)
Number of contacts Low Voltage	30
Gender	Reverse Gender

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/rak-3b-330-cll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Form & Material

Shell style / Model id	RA - Fixed coupler, nut fixing, keys (A) at the flange end and keys (A or K) at the other end
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Front side: 2 keys (alpha=30, female) , Other side: 2 keys (alpha=52.5, male)
Weight	81.32 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental protection (IP rating)	IP50
Minimal temperature	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Drawings



https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/rak-3b-330-cll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Dimensions

	A	B	e	E	L	M	S1	S3
mm.	25	27.5	M20x1.00	32	53	4	18.5	24
in.	0.98	1.08		1.26	2.09	0.16	0.73	0.94

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/rak-3b-330-cll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.