

Standard



*Image for illustrative purpose only*

## 概要

見積もりを依頼する

---

BKT series

Size

3K

---

シリーズ

K - Outdoor keyed

[https://www.lemo.com/int\\_jp/solutions/originals/k-outdoor-keyed/bfg-3k-100-ean.html](https://www.lemo.com/int_jp/solutions/originals/k-outdoor-keyed/bfg-3k-100-ean.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Form & Material

Shell style / Model id	BFG - Cap for plug
Keying	No keying
Colour	Black
Weight	7.56 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP61
Temperature range	-55°C / +135°C
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

## 図面

No keying

## 寸法

	A	L	N
mm.	24	30	155
になっています。	0.94	1.18	6.1

[https://www.lemo.com/int\\_jp/solutions/originals/k-outdoor-keyed/bfg-3k-100-ean.html](https://www.lemo.com/int_jp/solutions/originals/k-outdoor-keyed/bfg-3k-100-ean.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.