



Image for illustrative purpose only

概要

見積もりを依頼する

BKT series

Size

3K

シリーズ

K - Outdoor keyed

https://www.lemo.com/int_jp/solutions/originals/k-outdoor-keyed/bfr-3k-112-lds.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

Shell style / Model id	BFR - Cap for plug (R key)
Housing material	Aluminum alloy (anodized) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Keying	5 keys (alpha=95, beta=115, gamma=35, delta=25, plug: male contacts, receptacle: female contacts)
Weight	32.21 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

図面



寸法

	A	B	L	N
mm.	23	6	22	120
になっています。	0.91	0.24	0.87	4.72

https://www.lemo.com/int_jp/solutions/originals/k-outdoor-keyed/bfr-3k-112-lds.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.