

Special



*Image for illustrative purpose only*

## 概要

見積もりを依頼する

BKT series

Size

1K

シリーズ

K - Outdoor keyed

[https://www.lemo.com/int\\_jp/solutions/originals/k-outdoor-keyed/bre-1k-200-kav.html](https://www.lemo.com/int_jp/solutions/originals/k-outdoor-keyed/bre-1k-200-kav.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details


## Form & Material

Shell style / Model id	BRE - Cap for receptacle
Housing material	Brass (black chrome) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Keying	No keying
Colour	Black
Weight	17.28 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Temperature range	-40°C / +135°C
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## 図面



No keying

## 寸法

	A	B	L	M	N
mm.	17	12	20	6	85
になっています。	0.67	0.47	0.79	0.24	3.35

[https://www.lemo.com/int\\_jp/solutions/originals/k-outdoor-keyed/bre-1k-200-kav.html](https://www.lemo.com/int_jp/solutions/originals/k-outdoor-keyed/bre-1k-200-kav.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.