



Summary

[Request a quote](#)[Catalog](#)

Coax	1
Locking system	Push-pull
Matching parts	FFA.00.250.NTAC22
Series	00 - NIM-CAMAC

Technical details

Electrical Configuration

Coax	1
Insert configuration value	0.25 - 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated current	4 Amps
Impedance	50 Ohm
VSWR	$1.09 + 0.11 * f/\text{GHz}$
Vtest	2100 V (AC), 3000 V (DC)
Contact Type	Coaxial 50 Ohm
Contact Dia.	0.7 mm (0.03in)

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/aba-00-250-ntl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	ABA - Adapter from LEMO receptacle to BNC plug
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Weight	18.82 g

Environment

Environmental protection (IP rating)	IP50
Minimal temperature	-55°C / +260°C
F ret (min)	100 N
Salt Spray Corrosion	>144 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

Drawings



Dimensions

	A	L
mm.	14.5	28.5
in.	0.57	1.12

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/aba-00-250-ntl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.