



Image for illustrative purpose only

# Summary

[Request a quote](#)

[Catalog](#)

Size	0E
Series	E - Outdoor Stepped Insert

# Technical details


## Form & Material

Shell style / Model id	BFA - Cap for plug
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Keying	No keying
Colour	Grey
Weight	8.01 g

## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Temperature range	-50°C / +135°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>144 hr

# Drawings



No keying

## Dimensions

	A	B	L	N
mm.	14	6	12.5	85
in.	0.55	0.24	0.49	3.35

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/bfa-0e-100-nas.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/bfa-0e-100-nas.html)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.