



Image for illustrative purpose only

Summary

Request a quote	
Catalog	
Size	3K
Series	K - Outdoor keyed

Technical details

Form & Material

Shell style / Model id	BFG - Cap for plug
Keying	No keying
Colour	Black
Weight	7.56 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP61
Temperature range	-55°C / +135°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

Drawings

No keying

Dimensions

	A	L	N
mm.	24	30	155
in.	0.94	1.18	6.1