



Summary

[Request a quote](#)

[Catalog](#)

Size	3K
Series	K - Outdoor keyed

Technical details

Form & Material

Shell style / Model id	BFG - Cap for plug
Keying	No keying
Weight	7.56 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental protection (IP rating)	No IP rating
Minimal temperature	-55°C / +135°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/bfg-3k-100-ean.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings

No keying

Dimensions

	A	L	N
mm.	24	30	155
in.	0.94	1.18	6.1

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/bfg-3k-100-ean.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.