



Image for illustrative purpose only

# Summary

<a href="#">Request a quote</a>	
<a href="#">Catalog</a>	
Size	5M
Series	M - Rugged Ratchet coupling

# Technical details


## Form & Material

Shell style / Model id	BMF - Blanking cap for free receptacle(knurled grip)
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	19.74 g

## Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Temperature range	-55°C / +135°C
EMI Shielding EIA 364-66A	$\geq 80$ dB (1 GHz), $\geq 70$ dB (3 GHz), $\geq 58$ dB (6 GHz), $\geq 40$ dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [ 3 ms]
Thermal shock	5 cycles: -65°C to +150°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

## Drawings



[https://www.lemo.com/int\\_en/solutions/optima/m-ratchet-coupling/bmf-5m-200-xaz.html](https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/bmf-5m-200-xaz.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Dimensions

	A	C	L	N	P	X
mm.	34	33.5	31	150	3.4	10
in.	1.34	1.32	1.22	5.91	0.13	0.39