



Summary

[Request a quote](#)

[Catalog](#)

Technical details

Form & Material

Shell style / Model id	BRE - Cap for receptacle
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Keying	No keying
Weight	2.35 g


Environment

Environmental protection (IP rating)	IP61
Minimal temperature	-50°C / +135°C
Salt Spray Corrosion	>144 hr

https://www.lemo.com/int_en/bre-00-200-nas.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



No keying

Dimensions

	A	B	L	M	N
mm.	8	7.5	8.8	3.5	60
in.	0.31	0.3	0.35	0.14	2.36