



Image for illustrative purpose only

# Summary

<a href="#">Request a quote</a>	
<a href="#">Catalog</a>	
Size	3B
Series	B - Indoor keyed

# Technical details

## Form & Material

Shell style / Model id	BRE - Cap for receptacle
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Keying	No keying
Colour	Grey
Weight	22.7 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Temperature range	-50°C / +135°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>144 hr

# Drawings

No keying

## Dimensions

	A	B	L	M	N
mm.	22	25.5	17	7	95
in.	0.87	1	0.67	0.28	3.74

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/bre-3b-200-nas.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/bre-3b-200-nas.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.