



Image for illustrative purpose only

Summary

Request a quote	
Catalog	
Locking system	Threaded
Size	1V

Technical details


Form & Material

Shell style / Model id	BRF - Cap for receptacle
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Threaded
Keying	Circular, female
Colour	Grey
Weight	15.69 g

Environment

Environmental sealing (IP rating)	IP68
Temperature range	-20°C / +135°C
Climatical Category	20/200/21
Pressure	30 bars
Salt Spray Corrosion	>144 hr

Drawings



Dimensions

	A	L	N	S1
mm.	19.3	13.7	85	18
in.	0.76	0.54	3.35	0.71

https://www.lemo.com/int_en/brf-1v-200-nav.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.