



Image for illustrative purpose only

# Summary

[Request a quote](#)

[Catalog](#)

Locking system	Threaded
Size	4V

[https://www.lemo.com/int\\_en/brv-4v-200-cav.html](https://www.lemo.com/int_en/brv-4v-200-cav.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Form & Material

Shell style / Model id	BRV - Cap for receptacle
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	Circular, female
Colour	Grey
Weight	72.69 g

## Environment

Environmental sealing (IP rating)	IP68
Temperature range	-20°C / +135°C
Climatical Category	20/200/21
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

# Drawings



[https://www.lemo.com/int\\_en/brv-4v-200-cav.html](https://www.lemo.com/int_en/brv-4v-200-cav.html)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.