



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

https://www.lemo.com/int_en/dcp-t7-132-2ak.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

Keying	No keying
--------	-----------

Environment

Environmental sealing (IP rating)	No IP rating
Temperature range	-55°C / +250°C
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 20000 Hz]

Drawings

No keying