



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	2
Wire Size/AWG	30 - 22
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	0S
Matching parts	<a href="#">FFA.0S.302.CLAC22</a>
Series	S - Indoor Stepped Insert

## Technical details

### Electrical Configuration

Contact Termination Low voltage	PCB - Elbow
Insert configuration value	0S.302 - 2 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Vtest	1500 V (AC), 2100 V (DC)
Contact Type	Print (elbow)
Contact Dia.	0.9
Number of contacts Low Voltage	2
Wire Size/AWG	30 - 22

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/ecp-0s-302-clv.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-0s-302-clv.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Form & Material

Shell style / Model id	ECP - Fixed receptacle with two nuts, long threaded shell, with elbow contacts for printed circuit (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with female pin 1
Weight	5.29 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Drawings



[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/ecp-0s-302-clv.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-0s-302-clv.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Dimensions

	<b>E</b>	<b>M</b>	<b>e</b>	<b>A</b>	<b>B</b>	<b>S3</b>	<b>N</b>	<b>S1</b>
mm.	8.5	2.5	M9x0.6	12	12.5	11	15	8.2
in.	0.33	0.1		0.47	0.49	0.43	0.59	0.32

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/ecp-0s-302-clv.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-0s-302-clv.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.