



Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	10
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	3S
Matching parts	FFA.3S.310.CLAC62
Series	S - Indoor Stepped Insert

Technical details

Electrical Configuration

Contact Termination Low voltage	PCB - Straight
Insert configuration value	3S.310 - 10 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	9 Amps
Vtest	1060 V (AC), 1500 V (DC)
Contact Type	Print (straight)
Contact Dia.	1.3 mm (0.0512in)
Number of contacts Low Voltage	10

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-3s-310-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Form & Material

Shell style / Model id	ECP - Fixed receptacle with two nuts, long threaded shell, with straight contact for printed circuit (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with female pin 1
Weight	29.47 g

Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Drawings



https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-3s-310-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Dimensions

	M	N	E	A	B	e	S3	S1
mm.	4.5	24	14	24	25.2	M18x1.0	22	16.5
in.	0.18	0.94	0.55	0.94	0.99		0.87	0.65

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-3s-310-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.