



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|--------------------------------|--|
| Number of contacts Low Voltage | 4 |
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Rear Mounted |
| Locking system | Push-pull |
| Size | 0T |
| Suggested matching part | FGG.0T.304.CLAC50 |
| Series | T - Small Outdoor keyed |

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/eeg-0t-304-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------------|---------------------------|
| Number of contacts Low Voltage | 4 |
| Contact Termination Low voltage | PCB - Straight |
| R (max) | 6.1 mOhm |
| Insert configuration value | T.304 - 4 Low Voltage |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated current | 7 A |
| Vtest (contact-contact) | 850 V (AC), 1200 V (DC) |
| Vtest (contact-shell) | 700 V (AC), 1000 V (DC) |
| Contact Dia. | 0.7 mm (0.028in) |
| Gender | Standard |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | EE - Fixed receptacle, nut fixing, back panel mounting |
| Socket / Receptacle | Fixed Panel Rear Mounted |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Colour | Grey |
| Weight | 4.66 g |

Environment

| | |
|-----------------------------------|---|
| Technical domain | Energy and Industrial, Test and Measurement |
| Environmental sealing (IP rating) | IP68 |
| Endurance | >3000 mating cycles |
| Temperature range | -55°C / +200°C (max. temperature valid for short periods of use.) |
| Climatical Category | 50/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Resistance to vibration | 15 g [10 Hz - 2000 Hz] |
| Shock Resistance | 100 g [6 ms] |
| Salt Spray Corrosion | >1000 hr |

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/eeg-0t-304-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

| Accessories | |
|----------------|---|
| Compatible cap | BRE.0T.200.CAZ |
| Tools | |
| Spanner 2 | DCM.65.106.AZ4 |
| Spanner wrench | Socket for torque wrench DCM.0S.M09.4 |