



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	7
Wire Size/AWG	28 - 20
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	2K
Suggested matching part	<a href="#">FGG.2K.307.CLAC40</a>
Series	K - Outdoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/eeg-2k-307-clv.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-2k-307-clv.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	PCB - Elbow
R (max)	3.6 mOhm
Insert configuration value	2K.307 - 7 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Vtest (contact-contact)	1750 V (AC), 2500 V (DC)
Vtest (contact-shell)	1600 V (AC), 2250 V (DC)
Contact Type	Print (elbow)
Contact Dia.	1.3 mm (0.051in)
Number of contacts Low Voltage	7
Wire Size/AWG	28 - 20
Gender	Standard

## Form & Material

Shell style / Model id	EE - Fixed receptacle, nut fixing, with elbow contacts for printed circuit (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Weight	34.96 g


[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/eeg-2k-307-clv.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-2k-307-clv.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Drawings



## Dimensions

	<b>A</b>	<b>e</b>	<b>E</b>	<b>M</b>	<b>N</b>	<b>P</b>	<b>S1</b>	<b>B</b>
mm.	25	M20x1.0	5	3.5	26.6	10	18.5	25
in.	0.98		0.2	0.14	1.05	0.39	0.73	0.98

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/eeg-2k-307-clv.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-2k-307-clv.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.