



## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	7
Wire Size/AWG	26 - 22
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.80 - 10.70 mm
Size	1F
Matching parts	<a href="#">FGN.1F.307.CLC</a>
Series	F - Rugged Push-Pull

## Technical details

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/een-1f-307-clm.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/een-1f-307-clm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	Crimp
R (max)	6.1 mOhm
Insert configuration value	1F.307 - 7 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	7 Amps
Vtest (contact-contact)	1450 V (AC), 2050 V (DC)
Vtest (contact-shell)	1450 V (AC), 2050 V (DC)
Contact retention	22 N
Contact Type	Crimp
Max. Conductor	0.34 mm <sup>2</sup> (AWG 22)
Min. Conductor	0.14 mm <sup>2</sup> (AWG 26)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.7 mm (0.028in)
Number of contacts Low Voltage	7
Wire Size/AWG	26 - 22
Gender	Standard

## Form & Material

Shell style / Model id	EE - Fixed receptacle, nut fixing (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and nut, other pieces brass
Locking system	Push-pull
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	11.77 g

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/een-1f-307-clm.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/een-1f-307-clm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Motorsport, Security and Defence
Environmental protection (IP rating)	IP50
Minimal temperature	-55°C / +200°C
Climatical Category	50/175/21 (Aluminium shell)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Jacket cable outside diameter [mm]	3.80 - 10.70 mm
------------------------------------	-----------------

## Drawings



## Dimensions

	<b>B</b>	<b>e</b>	<b>E</b>	<b>S3</b>	<b>S2</b>	<b>A</b>	<b>S1</b>	<b>P</b>	<b>N</b>	<b>M</b>
mm.	15	M13x0.75	6.2	14	14	17	11.5	9.4	19	3.2
in.	0.59		0.24	0.55	0.55	0.67	0.45	0.37	0.75	0.13

## Recommended By Lemo

### Accessories

Replacement contact	<a href="#">EGG.0B.655.ZZM</a>
---------------------	--------------------------------










### Tools

Positionner	<a href="#">DCE.91.070.BVM</a>
Extraction tool	<a href="#">DCF.93.070.4LT</a>
Crimp tool	<a href="#">DPC.91.701.V</a>

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/een-1f-307-clm.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/een-1f-307-clm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

Cable PartNumber	Material	Colour	Cable image
CMN.07.T26.037QGZE	TPR (medical)	Grey	
CMN.07.T28.044PGZE		grey	
CMN.07.T28.044PNZE			
270250	PVC	Grey	
70140	PVC	Grey	
7041	PVC	Grey	
7050	PVC	Black	
717920	PVC	Grey	
CTR.75.030.121875G	PVC	Grey	

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/een-1f-307-clm.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/een-1f-307-clm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.