



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	1
Wire Size/AWG	32 - 28
Size	00
Suggested matching part	FGG.00.554.ZZC
Series	00 - NIM-CAMAC

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/egg-00-654-zzm.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Contact Termination Low voltage	Crimp
Contact Dia.	0.5
Number of contacts Low Voltage	1
Wire Size/AWG	32 - 28

Form & Material

Shell style / Model id	EG - Female crimp contact, standard barrel
Housing material	Gold plated [ISO 27874] bronze
Keying	No keying
Weight	0.04 g

Environment

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

Recommended By Lemo

Tools

Positionner	DCE.91.050.0VM
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/egg-00-654-zzm.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.