



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	1
Wire Size/AWG	32 - 28
Size	00
Suggested matching part	<a href="#">FGG.00.554.ZZC</a>
Series	00 - NIM-CAMAC

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/egg-00-654-zzm.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/egg-00-654-zzm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Contact Dia.	0.5
Wire Size/AWG	32 - 28

## Form & Material

Shell style / Model id	EG - Female crimp contact, standard barrel
Housing material	Gold plated [ISO 27874] bronze
Keying	No keying
Weight	0.04 g

## Environment

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

# Recommended By Lemo

## Tools

Positionner	<a href="#">DCE.91.050.0VM</a>
Crimp tool	<a href="#">DPC.91.701.V</a>

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/egg-00-654-zzm.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/egg-00-654-zzm.html)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.