



Image for illustrative purpose only

Summary

Request a quote	
Catalog	
Number of contacts Low Voltage	1
Wire Size/AWG	32 - 28
Size	0B
Series	B - Indoor keyed

Technical details

Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Contact Dia.	0.5
Wire Size/AWG	32 - 28

Form & Material

Shell style / Model id	EG - Female crimp contact, standard barrel
Housing material	Gold plated [ISO 27874] bronze
Keying	No keying
Weight	0.06 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Humidity (max)	<=95% [at 60 deg C /140 F]

Recommended By Lemo

Tools

Positionner	DCE.91.050.BVM
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/egg-0b-654-zzm.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.