



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Thermocouple	1
Wire Size/AWG	26 - 22
Size	0B
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/egg-0b-655-zzk.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Thermocouple	1
Contact Termination Thermocouple	Crimp
Contact Dia.	0.7
Wire Size/AWG	26 - 22

Form & Material

Shell style / Model id	EG - Type K thermocouple female crimp contact, standard barrel
Housing material	Thermocouple / Chromel
Keying	No keying
Weight	0.21 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Humidity (max)	<=95% [at 60 deg C /140 F]

Recommended By Lemo

Tools

Positionner	DCE.91.070.BVM
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/egg-0b-655-zzk.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.