



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	1
Locking system	Push-pull
Size	0R

https://www.lemo.com/int_en/egg-0r-250-zlce28.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Crimp
Insert configuration value	1 coax - 50 Ohm
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	2.5 A
OHM	50
VSWR	<1.25 DC to 8 GHz <1.5 8 to 26.5 GHz
Test voltage (KV rms) Contact-Screen	0.95
Cable type	RG-174/U , RG-188 A/U , RG-316/U , LMR-100A , Multiflex_86

Form & Material

Locking system	Push-pull
Keying	No keying
Weight	1.81 g

Environment

Environmental sealing (IP rating)	IP50
Cable Group	1
Conductor ø max	0.54 mm
Dielectric ø max	1.54 mm
Sheath ø max	2.8 mm

Recommended By Lemo

Tools

Positionner	DCE.91.050.RVCM
Extraction tool	DCC.91.C0R.LAG
Crimp tool	DPC.91.701.V
Crimp Tool 2	DPE.99.003.1K

https://www.lemo.com/int_en/egg-0r-250-zlce28.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.