



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

|                            |   |
|----------------------------|---|
| Nb of contacts Fiber optic | 2   |
| Gender                     | Standard  |
| Socket / Receptacle        | Socket / Receptacle - Fixed Panel Front Mounted |
| Locking system             | Push-pull                                       |
| Size                       | 3K  |
| Suggested matching part    | <a href="#">FGG.3K.03A.CLZT66Z</a>              |
| Series                     | K - Outdoor keyed                               |

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/egg-3k-03a-clz.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/egg-3k-03a-clz.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                            |                                   |
|----------------------------|-----------------------------------|
| Nb of contacts Fiber optic | 2                                 |
| Insert configuration value | 3K.03A - 2 FO Type F2 (<= 140 um) |
| Insulator                  | L: PEEK (UL 94 / V-0/1.5)         |
| Gender                     | Standard                          |

## Form & Material

|                        |  |
|------------------------|--|
| Shell style / Model id | EG - Fixed receptacle, nut fixing  |
| Socket / Receptacle    | Fixed Panel Front Mounted  |
| Housing material       | Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces |
| Locking system         | Push-pull  |
| Keying                 | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)   |
| Colour                 | Grey   |
| Weight                 | 65.67 g  |

## Environment

|                                   |   |
|-----------------------------------|---|
| Technical domain                  | Audio Video, Energy and Industrial, Medical, Test and Measurement |
| Environmental sealing (IP rating) | IP68  |
| Endurance                         | 5000 mating cycles  |
| Temperature range                 | -55°C / +200°C (max. temperature valid for short periods of use.) |
| Climatical Category               | 50/175/21   |
| Humidity (max)                    | <=95% [at 60 deg C /140 F]  |
| Shielding (min)                   | 95 dB (10 MHz)  |
| Shielding (min)                   | 80 dB (1 GHz)   |
| Shock Resistance                  | 100 g [ 6 ms]   |
| Vibration                         | 15 g [10 Hz - 2000 Hz]  |
| Salt Spray Corrosion              | >1000 hr  |

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/egg-3k-03a-clz.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/egg-3k-03a-clz.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

---

|                |                                |
|----------------|--------------------------------|
| Compatible cap | <a href="#">BRE.3K.200.NAS</a> |
|----------------|--------------------------------|