



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	17
Nb of contacts Coax	2
Wire Size/AWG	16 - 12
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.00 - 33.60 mm
Size	5B
Series	B - Indoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/egg-5b-857-clm6.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/egg-5b-857-clm6.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	17
Contact Termination Low voltage	Crimp
Nb of contacts Coax	2
Contact Termination Coax - Conductor fixing	Solder
Contact Termination Coax - Screen fixing	Crimp
Insert configuration value	5B.857 - 2 Coax (50 Ohm), 17 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Test voltage (kV DC)	2
Cable type	RG 58 C/U
Contact Dia.	2
Wire Size/AWG	16 - 12
Gender	Standard

## Form & Material

Shell style / Model id	EG - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	237.42 g

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/egg-5b-857-clm6.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/egg-5b-857-clm6.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Jacket cable outside diameter [mm]	4.00 - 33.60 mm
------------------------------------	-----------------

## Drawings



## Dimensions

	<b>e</b>	<b>E</b>	<b>L</b>	<b>M</b>	<b>N</b>	<b>S1</b>	<b>B</b>	<b>A</b>
mm.	M35x1.0	11	43.5	3	39.6	33.5	40	40
in.		0.43	1.71	0.12	1.56	1.32	1.57	1.57

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/egg-5b-857-clm6.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/egg-5b-857-clm6.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

Replacement contact	<a href="#">EGG.5B.660.ZZM</a>
Compatible cap	<a href="#">BRE.5S.200.NAS</a>

## Tools

Die Tool	<a href="#">DPE.99.176.2K</a>
Positionner	<a href="#">DCE.91.205.BVCM</a>
Positionner 2	<a href="#">DCE.91.095.BVM</a>
Extraction tool	<a href="#">DCC.09.05B.LAG</a>
Extraction tool 2	<a href="#">DCC.91.203.5LT</a>
Crimp tool	<a href="#">DPC.91.701.V</a>
Crimp Tool 2	<a href="#">DPC.91.101.A</a>
Spanner wrench	<a href="#">Socket for torque wrench DCM.65.370.AZ</a>

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/egg-5b-857-clm6.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/egg-5b-857-clm6.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.