



Summary

[Request a quote](#)

[Catalog](#)

Fluidic	1
Size	P1
Matching parts	FGG.P1.150.ACV

Technical details

Electrical Configuration

Fluidic	1
---------	---

Form & Material

Shell style / Model id	EGG - Female fluidic contact with valve
Housing material	Body: Stainless steel, Valve: Alloy CuNiZn, Spring: Stainless steel, Clips: CuBe, O-ring: FPM
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	4.23 g

Environment

Environmental protection (IP rating)	IP50
Minimal temperature	-20°C / +125°C

https://www.lemo.com/int_en/egg-p1-150-acv.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.