



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|---|
| Number of contacts Low Voltage | 4 |
| Wire Size/AWG | 16 - 12 |
| Gender | Reverse Gender |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Front Mounted |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 2.00 - 16.60 mm |
| Size | 3T |
| Suggested matching part | FGL.3T.304.CYMC10 |
| Series | T - Small Outdoor keyed |

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/egl-3t-304-cyc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------------|------------------------------|
| Number of contacts Low Voltage | 4 |
| Contact Termination Low voltage | Crimp |
| R (max) | 3.3 mOhm |
| Insert configuration value | T.304 - 4 Low Voltage |
| Insulator | Y: PEEK for crimp contacts |
| Rated current | 17 A |
| Vtest (contact-contact) | 3.4 kV (DC) |
| Vtest (contact-shell) | 2.5 kV (DC) |
| Contact retention | 65 N |
| Max. Conductor | 2.5 mm ² (AWG 12) |
| Min. Conductor | 1.5 mm ² (AWG 16) |
| Bucket Dia. | 2.4 mm (0.094in) |
| Contact Dia. | 2 mm (0.079in) |
| Wire Size/AWG | 16 - 12 |
| Gender | Reverse Gender |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | EG - Fixed receptacle, nut fixing |
| Socket / Receptacle | Fixed Panel Front Mounted |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | L: 2 keys (gamma=70, plug: female contacts, receptacle: male contacts) |
| Colour | Grey |
| Weight | 14.41 g |

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/egl-3t-304-cyc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

| | |
|-----------------------------------|---|
| Environmental sealing (IP rating) | IP68 |
| Endurance | >3000 mating cycles |
| Temperature range | -55°C / +200°C (max. temperature valid for short periods of use.) |
| Climatical Category | 50/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Resistance to vibration | 15 g [10 Hz - 2000 Hz] |
| Shock Resistance | 100 g [6 ms] |
| Salt Spray Corrosion | >1000 hr |

Cable fixation

| | |
|------------------------------------|-----------------|
| Jacket cable outside diameter [mm] | 2.00 - 16.60 mm |
|------------------------------------|-----------------|

Drawings



Dimensions

| | A | B | e | E | L | M | N | S1 | S2 |
|-----|------|------|---------|------|------|-----|------|------|------|
| mm. | 23.5 | 25.1 | M18x1.0 | 9.6 | 30.1 | 2.5 | 25 | 16.5 | 22 |
| in. | 0.93 | 0.99 | | 0.38 | 1.19 | 0.1 | 0.98 | 0.65 | 0.87 |

Recommended By Lemo

Accessories

| | |
|---------------------|--------------------------------|
| Replacement contact | FGG.3B.575.ZZC |
| Compatible cap | BRE.3T.200.CAZ |

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/egl-3t-304-cyc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.




















Tools

| | |
|-----------------|---------------------------------|
| Positionner | DCE.91.203.BVCM |
| Extraction tool | DCC.20.25B.LAG |
| Crimp tool | DPC.91.101.A |

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/egl-3t-304-cyc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

| Cable PartNumber | Material | Colour | Cable image |
|--------------------|---------------|--------|---|
| CMN.04.T14.083PGZE | | grey |  |
| CMN.04.T14.083PNZE | | |  |
| CMN.04.T20.053PGZE | | grey |  |
| CMN.04.T20.053PNZE | | |  |
| CMN.04.T20.053QGZE | TPR (medical) | Grey |  |
| CMN.04.T22.047QGC | TPR | Grey | |
| CMN.04.T22.048QGZE | TPR (medical) | Grey |  |
| CMN.04.T28.031PGCE | PVC | GREY |  |
| CMN.04.T28.031PGZE | | grey |  |
| CMN.04.T28.031PNCE | PVC | Black |  |
| CMN.04.T28.031PNZE | | |  |
| CMN.04.T28.031QGC | TPR | Grey | |
| 140240 | PVC | Black |  |
| 140250 | PVC | Grey |  |
| 240500 | PVC | Grey |  |
| 240750 | PVC | Grey |  |
| 340 150 | PVC | Grey |  |
| 40080 | PVC | Black | |
| 40086 | PVC | Blue | |
| 40140 | PVC | Black |  |
| 40240 | PTFE | White |  |
| 40260 | PVC | Black |  |
| 4041 | PVC | Grey |  |
| 4050 | PVC | Black |  |
| 4080 | PVC | Grey | |
| 417920 | PVC | Grey |  |
| 4220 | PVC | Black |  |
| 4221 | PVC | Black |  |
| 4260 | PTFE | White |  |
| 4280 | PVC | Black |  |
| 80080 | PVC | Grey | |
| 80082 | PVC | Red | |
| 80084 | PVC | Black | |
| CTR.75.030.121870G | PVC | Grey |  |

https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/egl-3t-304-cyc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.