



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	1
Wire Size/AWG	20 - 18
Jacket cable outside diameter [mm]	3.80 - 10.70 mm
Size	1F
Series	F - Rugged Push-Pull

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/egn-1f-665-zzm.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/egn-1f-665-zzm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Contact Dia.	1.3
Wire Size/AWG	20 - 18

## Form & Material

Shell style / Model id	EG - Female crimp contact for F series, standard barrel
Housing material	Gold plated [ISO 27874] bronze
Keying	No keying
Weight	0.25 g

## Environment

Technical domain	Motorsport, Security and Defence
Environmental sealing (IP rating)	No IP rating

## Cable fixation

Jacket cable outside diameter [mm]	3.80 - 10.70 mm
------------------------------------	-----------------

# Recommended By Lemo

## Tools

Crimp tool	<a href="#">DPC.91.701.V</a>
------------	------------------------------

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/egn-1f-665-zzm.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/egn-1f-665-zzm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.