



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

| | |
|------------------------------------|---|
| Number of contacts Low Voltage | 16 |
| Wire Size/AWG | 26 - 22 |
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Front Mounted |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 2.00 - 13.60 mm |
| Size | 2B |
| Suggested matching part | FGY.2B.316.PYCD9BZ |
| Series | B - Indoor keyed |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/eny-2b-316-pymb.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage | 16 |
| Contact Termination Low voltage | Crimp |
| R (max) | 6.1 mOhm |
| Insert configuration value | 2B.316 - 16 Low Voltage |
| Insulator | Y: PEEK for crimp contacts |
| Rated current | 6 A |
| Vtest (contact-contact) | 2.2 kV (DC) |
| Vtest (contact-shell) | 2.5 kV (DC) |
| Contact retention | 22 N |
| Max. Conductor | 0.34 mm ² (AWG 22) |
| Min. Conductor | 0.14 mm ² (AWG 26) |
| Bucket Dia. | 0.8 mm (0.031in) |
| Contact Dia. | 0.7 mm (0.028in) |
| Wire Size/AWG | 26 - 22 |
| Gender | Standard |

Form & Material

| | |
|------------------------|--|
| Shell style / Model id | ENY - Fixed receptacle with grounding tab, nut fixing, PSU or PPSU outer shell |
| Socket / Receptacle | Fixed Panel Front Mounted |
| Housing material | PSU (Polysulfone) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | 3 keys (beta=112.5, gamma=100, plug: male contacts, receptacle: female contacts) |
| Weight | 9.54 g |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/eny-2b-316-pymb.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Environment

| | |
|-----------------------------------|--|
| Technical domain | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50 |
| Endurance | 5000 mating cycles |
| Temperature range | -50°C / +150°C |
| Climatical Category | 50/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shielding (min) | 75 dB (10 MHz) |
| Shielding (min) | 40 dB (1 GHz) |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 2000 Hz] |

Cable fixation

| | |
|------------------------------------|-----------------|
| Jacket cable outside diameter [mm] | 2.00 - 13.60 mm |
|------------------------------------|-----------------|

Drawings



Dimensions

| | A | B | e | E | L | M | N | S1 | S3 |
|-----|------|------|---------|------|------|------|------|------|------|
| mm. | 18 | 19.5 | M15x1.0 | 8.5 | 26.7 | 1.8 | 24.6 | 13.5 | 17 |
| in. | 0.71 | 0.77 | | 0.33 | 1.05 | 0.07 | 0.97 | 0.53 | 0.67 |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/eny-2b-316-pymb.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories

| | |
|---------------------|--------------------------------|
| Replacement contact | EGG.2B.655.ZZM |
|---------------------|--------------------------------|











Tools

| | |
|-------------|--------------------------------|
| Positionner | DCE.91.072.BVM |
|-------------|--------------------------------|

| | |
|-----------------|--------------------------------|
| Extraction tool | DCC.07.04B.LAG |
|-----------------|--------------------------------|

| | |
|------------|------------------------------|
| Crimp tool | DPC.91.701.V |
|------------|------------------------------|

Cables

| Cable PartNumber | Material | Colour | Cable image |
|--------------------|---------------|--------|---|
| CMN.16.T22.076QGZE | TPR (medical) | Grey |  |
| CMN.16.T28.059PGZE | | grey |  |
| CMN.16.T28.059PNZE | | |  |
| CMN.16.T28.070NNZZ | | | |
| CMN.16.T30.047QGZE | TPR (medical) | Grey |  |
| 116080 | PUR | Black | |
| 116280 | PVC | Black |  |
| 16050 | PVC | Black |  |
| 216220 | PVC | Black |  |
| 216240 | PVC | Black |  |
| 216260 | PVC | Black |  |
| 316250 | PVC | Grey |  |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/eny-2b-316-pymb.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.