



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	1
Socket / Receptacle	Socket / Receptacle - Elbow
Locking system	Push-pull
Size	1
Suggested matching part	FFS.01.250.DLAE31

https://www.lemo.com/int_en/epl-01-250-dln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
Insert configuration value	1.25 - 1 Coax (50 Ohm)
Rated current	4 A
OHM	50

Form & Material

Shell style / Model id	EPL.01 - Elbow receptacle for printed circuit
Socket / Receptacle	Elbow
Housing material	Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Weight	3.17 g

Environment

Environmental sealing (IP rating)	IP50
Endurance	1000 mating cycles
Temperature range	-55°C / +230°C

Drawings



Dimensions

	A	L	M	B	C	D	N
mm.	6	12.5	8.5	6	6	10	3
in.	0.24	0.49	0.33	0.24	0.24	0.39	0.12

https://www.lemo.com/int_en/epl-01-250-dln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.