



## Summary

[Request a quote](#)

---

[Catalog](#)

---

Nb of contacts Coax	1
Locking system	Push-pull
Size	0A

[https://www.lemo.com/int\\_en/eps-0a-275-ntn.html](https://www.lemo.com/int_en/eps-0a-275-ntn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Insert configuration value	0A.275 - 1 Coax (75 Ohm)
Rated current	2 A

## Form & Material

Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	10.43 g

## Environment

Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Salt Spray Corrosion	>144 hr

[https://www.lemo.com/int\\_en/eps-0a-275-ntn.html](https://www.lemo.com/int_en/eps-0a-275-ntn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.