



Image for illustrative purpose only

## Summary

[Request a quote](#)

Number of contacts Low Voltage	7
Number of contacts High Voltage	2
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.00 - 23.60 mm
Size	4S
Suggested matching part	<a href="#">FFA.4S.737.CJLC13</a>
Series	S - Indoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/era-4s-737-cja.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/era-4s-737-cja.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	Solder
Contact Termination High voltage	Solder
Insert configuration value	4S.737 - 2 High Voltage, 7 Low Voltage
Insulator	J: PEEK/PEEK
Rated current	LV 9, HV 14 A
Test voltage LV Ue (kV rms)	3
Working voltage HV contact - Us (kV rms)	2.1
Contact Type	Solder
Number of contacts Low Voltage	7
Number of contacts High Voltage	2
Note performance	Please use heatshrink to guarantee High Voltage performance.

## Form & Material

Shell style / Model id	ERA - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with male pin 1
Colour	Grey
Weight	57.25 g

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/era-4s-737-cja.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/era-4s-737-cja.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Jacket cable outside diameter [mm]	3.00 - 23.60 mm
------------------------------------	-----------------

## Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>E</b>	<b>L</b>	<b>M</b>	<b>S1</b>	<b>S3</b>
mm.	28	34	M25x1.0	12	34	2.5	23.5	30
in.	1.1	1.34		0.47	1.34	0.1	0.93	1.18

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/era-4s-737-cja.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/era-4s-737-cja.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.