



## Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	4
Number of contacts Low Voltage	26
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.00 - 45.60 mm
Size	6S
Matching parts	<a href="#">FFA.6S.882.CLAC183</a>
Series	S - Indoor Stepped Insert

## Technical details

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/era-6s-882-cll5.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/era-6s-882-cll5.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Contact Termination Low voltage	Solder
Nb of contacts Coax	4
Contact Termination Coax	Solder
Insert configuration value	6S.882 - 4 Coax (75 Ohm), 26 LV
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	2 Amps
Impedance	75 Ohm
Vtest	2400 V (AC), 3300 V (DC)
Vtest (contact-shell)	750 V (AC), 1100 V (DC)
Cable type	Cable type: A RG 59 B/U, RG 302 /U, RG 400 /U S
Number of contacts Low Voltage	26

## Form & Material

Shell style / Model id	ERA - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with female pin 1
Weight	260.59 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/era-6s-882-cll5.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/era-6s-882-cll5.html)



LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Jacket cable outside diameter [mm]

5.00 - 45.60 mm

## Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>E</b>	<b>L</b>	<b>M</b>	<b>S1</b>
mm.	54	54	M48x1.5	16	45	3.5	45.5
in.	2.13	2.13		0.63	1.77	0.14	1.79

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/era-6s-882-cll5.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/era-6s-882-cll5.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.