



Image for illustrative purpose only

Summary

[Request a quote](#)

Nb of contacts Triax	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.80 - 28.60 mm
Size	4E
Suggested matching part	FFA.4E.675.CTAC11Z
Series	E - Outdoor Stepped Insert

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ern-4e-675-ctl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Triax	1
Contact Termination Triax	Solder
Insert configuration value	4E.675 - 1 Triax (75 Ohm)
Insulator	T: PTFE
Rated current	15 A
Impedance	75 Ohm
OHM	75
VSWR	$1.01 + 0.14 * f/\text{GHz}$
Vtest	1500 V (AC), 2120 V (DC)
Cable type	Belden 8215,8232A,HF-2426,Triax 8 Nokia,375 029 LEDE, Belden 9267,8233A, Triax 11 Nokia,466 140 LEDE

Form & Material

Shell style / Model id	ERN - Fixed receptacle with tag, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Weight	102.62 g

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ern-4e-675-ctl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP66
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	55/175/21
F ret (min)	90 N
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	85 dB (10 MHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Jacket cable outside diameter [mm]	4.80 - 28.60 mm
------------------------------------	-----------------

Drawings



Dimensions

	A	L	e
mm.	37	39	M30x1
in.	1.46	1.54	

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ern-4e-675-ctl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.