



Summary

[Request a quote](#)

[Catalog](#)

Fluidic	1
Number of contacts Low Voltage	10
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Threaded
Size	2W
Matching parts	FVG.2W.P15.CLAC85
Series	W - Underwater

Technical details

Electrical Configuration

Contact Termination Low voltage	Solder
Fluidic	1
Contact Termination Fluidic	Solder
Insert configuration value	2W.P15 - 1 Fluidic with valve P1, 10 Low Voltage
Contact Type	Solder
Number of contacts Low Voltage	10
Gender	Standard

https://www.lemo.com/int_en/solutions/supreme/w-underwater/evg-2w-p15-cll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Form & Material

Shell style / Model id	EV - Fixed socket, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	1 key (alpha=0, Plug: male contacts, Receptacle: female contacts)
Weight	23.74 g

Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C
Climatical Category	20/200/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

Drawings



https://www.lemo.com/int_en/solutions/supreme/w-underwater/evg-2w-p15-cll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Dimensions

	A	B	e	e1	E	L	N	S1	S2	S3
mm.	22.5	21.8	M16x1.0	M20x1.0	9	30.7	9	14.5	18.5	19
in.	0.89	0.86			0.35	1.21	0.35	0.57	0.73	0.75

https://www.lemo.com/int_en/solutions/supreme/w-underwater/evg-2w-p15-cll.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.