



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Fiber optic	2
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Threaded
Size	3W
Series	W - Underwater

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/evg-3w-93e-cll.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/evg-3w-93e-cll.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Fiber optic	2
Contact Termination Fiber optic	Solder
Contact Type	Solder
Gender	Standard

## Form & Material

Shell style / Model id	EV - Fixed socket, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	G: 1 key (alpha=0, Plug: male contacts, Receptacle: female contacts)
Colour	Grey
Weight	42.97 g



## Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C
Climatical Category	20/200/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/evg-3w-93e-cll.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/evg-3w-93e-cll.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>e1</b>	<b>E</b>	<b>L</b>	<b>N</b>	<b>S1</b>	<b>S2</b>	<b>S3</b>
mm.	26.6	27	M20x1.0	M24x1.0	13	36.2	9.5	18.5	22.5	24
in.	1.05	1.06			0.51	1.43	0.37	0.73	0.89	0.94

[https://www.lemo.com/int\\_en/solutions/supreme/w-underwater/evg-3w-93e-cll.html](https://www.lemo.com/int_en/solutions/supreme/w-underwater/evg-3w-93e-cll.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.