



Summary

[Request a quote](#)

[Catalog](#)

Triax	1
Locking system	Push-pull
Size	T7

Technical details

Electrical Configuration

Triax	1
Contact Termination Triax	Solder
Rated current	12 Amps
Contact Type	Solder

Form & Material

Shell style / Model id	FAZ - Plug, collet clamp
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	212.99 g

https://www.lemo.com/int_en/faz-t7-675-cta02c.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 20000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet

Drawings



Dimensions

	A	L	S1	S2
mm.	23.5	86	22	20
in.	0.93	3.39	0.87	0.79

https://www.lemo.com/int_en/faz-t7-675-cta02c.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.