



## Summary

[Request a quote](#)

[Catalog](#)

Triax	1
Locking system	Push-pull
Size	T7

## Technical details

### Electrical Configuration

Triax	1
Contact Termination Triax	Solder
Rated current	12 Amps
Contact Type	Solder

### Form & Material

Shell style / Model id	FAZ - Plug, crimp, nut for fitting a bend relief
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male

[https://www.lemo.com/int\\_en/faz-t7-675-cta05sz.html](https://www.lemo.com/int_en/faz-t7-675-cta05sz.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 20000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet

## Drawings



## Dimensions

	<b>A</b>	<b>L</b>	<b>S1</b>	<b>S2</b>
mm.	23.5	87.5	22	20
in.	0.93	3.44	0.87	0.79

[https://www.lemo.com/int\\_en/faz-t7-675-cta05sz.html](https://www.lemo.com/int_en/faz-t7-675-cta05sz.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.