



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Triax	1
Plug	Plug - Fixed
Locking system	Push-pull
Size	4A

https://www.lemo.com/int_en/fbf-4a-675-ctaz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Triax	1
Contact Termination Triax	Solder
Insert configuration value	4A.675 - 1 Triax (75 Ohm)
Insulator	T: PTFE
Rated current	6 A
Impedance	75 Ohm
OHM	75
Vtest	1200 V (AC), 1690 V (DC)

Form & Material

Shell style / Model id	FBF - Fixed plug with round flange and tag, nut fixing
Plug	Fixed
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Colour	Grey
Weight	129.57 g

Environment

Environmental sealing (IP rating)	IP61
Endurance	5000 mating cycles
Climatical Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Salt Spray Corrosion	>1000 hr


Cable fixation

Fixation type	Cable collet
---------------	--------------

https://www.lemo.com/int_en/fbf-4a-675-ctaz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

	L	M	e	A
mm.	65	47.8	M25x1.0	35
in.	2.56	1.88		1.38