



Image for illustrative purpose only

Summary

[Request a quote](#)

[REDEL T7 en](#)

| | |
|----------------------|--------------|
| Nb of contacts Triax | 1 |
| Plug | Plug - Fixed |
| Locking system | Push-pull |
| Panel Drill Hole | M25 |
| Size | T7 |

https://www.lemo.com/int_en/fez-t7-675-cta04c.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------|---------|
| Nb of contacts Triax | 1 |
| Contact Termination Triax | Solder |
| Rated current | 12 A |
| Impedance | 75 Ohms |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | FEZ - Fixed plug, collet clamp, nut fixing |
| Plug | Fixed |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | Circular, male |
| Colour | Grey |
| Panel Drill Hole | M25 |

Environment

| | |
|-----------------------------------|---|
| Environmental sealing (IP rating) | IP68 |
| Endurance | 5000 mating cycles |
| Temperature range | -55°C / +250°C (max. temperature valid for short periods of use.) |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 20000 Hz] |
| Salt Spray Corrosion | >1000 hr |

Cable fixation

| | |
|------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
| Fixation type | Cable collet |

https://www.lemo.com/int_en/fez-t7-675-cta04c.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

| | A | E | L | M | S1 | S2 | e |
|-----|----------|----------|----------|----------|-----------|-----------|----------|
| mm. | 30 | 6 | 86 | 22.4 | 22 | 20 | M25x1.0 |
| in. | 1.18 | 0.24 | 3.39 | 0.88 | 0.87 | 0.79 | |

https://www.lemo.com/int_en/fez-t7-675-cta04c.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.