



## Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	1.80 - 2.20 mm
Matching parts	<a href="#">ERA.00.250.NLL</a>
Series	00 - NIM-CAMAC

## Technical details

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/ffa-00-250-nlac22.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/ffa-00-250-nlac22.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Electrical Configuration

Coax	1
Contact Termination Coax	Solder
R (max)	6.1 mOhm
Insert configuration value	0.25 - 1 Coax (50 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	4 Amps
Impedance	50 Ohm
VSWR	1.09 + 0.11 * f/GHz
Vtest	2100 V (AC), 3000 V (DC)
Contact Type	Coaxial 50 Ohm (Solder)
Test voltage	2.1 kV (rms)
Cable type	Cable type: A RG 196 A/U - RG 178 B/U - LEMO Germany reference 178 190 S
Bucket Dia.	0.6 mm (0.024in)
Contact Dia.	0.7 mm (0.028in)

## Form & Material

Shell style / Model id	FFA - Straight plug with cable collet
Plug	Straight
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	2.84 g

## Environment

Environmental protection (IP rating)	IP50
F ret (min)	100 N
Salt Spray Corrosion	>144 hr


## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	1.80 - 2.20 mm

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/ffa-00-250-nlac22.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/ffa-00-250-nlac22.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Drawings



## Dimensions

	A	L	M
mm.	6.4	26	18
in.	0.25	1.02	0.71

## Recommended By Lemo

### Accessories

### Tools

Spanner wrench

[DCD.00.ZZZ.PA045](#)

## Cables

Cable PartNumber	Material	Colour	Cable image
178190	PTFE	Brown	
196270	PTFE	White	
CCX.50.030.083.180B		white	
CCX.50.RG1.78BU18M	FEP	Brown	
CCX.50.RG1.78BU18M	PTFE	Brown	
CCX.50.RG1.96AU19B	PTFE	White	
CCX.50.RG1.96AU20B	PFA	White	

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/ffa-00-250-nlac22.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/ffa-00-250-nlac22.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.